

RTE Config H301



Description of Configuration File

Basics

- Device Type: B60
- Protocol: PROFINET

Slot Configuration

- 8 Bytes Input: Device Status
- 8 Bytes Input: Status of Processing Instance
- 16 Bytes Input: User-Defined Process Data
- 64 Bytes Input: User-Defined Process Data
- 4 Bytes Output: Commands
- 4 Bytes Output: User-Defined Process Data
- 64 Bytes Output: User-Defined Process Data

User-Defined Process Data Input (Device to PLC)

- 4 Bytes: 32 BOOL
- 4 Bytes: 1 DINT
- 8 Bytes: 2 REAL
- 64 Bytes: 1 CHAR with 64 Bytes

User-Defined Process Data Output (PLC to Device)

- 4 Bytes: 32 BOOL
- 64 Bytes: 1 CHAR with 64 Bytes



NOTE!

For common info (e.g. status and command bits) check the interface protocol.