


Firmware weCat3D



Release Notes

Subject to change without notice
Available as PDF only
Version 1.3.5
Status: 26.01.2026
www.wenglor.com

Compatibility

The firmware version number consists of three digits (e.g. Firmware weCat3D 1.0.0).

- Major release: The first digit is changed (no compatability).
- Feature release: The second digit is changed.
- Bugfix release: The third digit is changed.

Change Index Firmware weCat3D

Version	Release Date	Description
1.3.5	26.01.2026	<ul style="list-style-type: none">• Bugfixes• Minor improvements
1.3.4	10.12.2025	<ul style="list-style-type: none">• Bugfixes• Minor improvements
1.3.3	03.04.2025	<ul style="list-style-type: none">• Bugfix for small container size and small bandwith• Minor improvements
1.3.2	24.02.2025	<ul style="list-style-type: none">• AutoExposureMode stabilization• Added maximum frame rate in xml• Bugfixes• Minor improvements
1.3.1	20.11.2024	<ul style="list-style-type: none">• Bugfixes• Minor improvements
1.3.0	06.11.2024	<ul style="list-style-type: none">• New commands:<ul style="list-style-type: none">» SetContainerContent: Option to reduce the amount of transmitted sensor data» SetSignalContentSwap: Option to switch the order of the transmitted data<ul style="list-style-type: none">♦ Example: SetSignalContentSwap=0: standard SetSignalContentSwap=1: swap intern from hi/lo to lo/hi• New commands for MLWL<ul style="list-style-type: none">» SetEthernetSpeedUp: Option to enable the MLWL to be operated with a measurement rate of up to 6kHz• Minor improvements
1.2.7	11.09.2023	<ul style="list-style-type: none">• Support of special devices• "SetCameraMode" (deprecated) is replaced by "SetOperatingMode"• Minor improvements